



Rubber- and PVC hoses for Food technique							Art.No	EUR	Art.No	EUR
<b>Silicone pharmacy laboratory hose</b> 	DN	A	B	C	Pressure bar, 20 °C	Vacuum bar, 20 °C			VMQ	
	2x1	4	2	1	-	-			6115-2x1	Enquiry
	3x1	5	3	1	-	-			6115-3x1	Enquiry
	4x1,5	7	4	1,5	-	-			6115-4x1,5	Enquiry
	4x2	8	4	2	-	-			6115-4x2	Enquiry
	5x1,5	8	5	1,5	-	-			6115-5x1,5	Enquiry
	5x2	9	5	2	-	-			6115-5x2	Enquiry
	6x1,5	9	6	1,5	-	-			6115-6x1,5	Enquiry
	6x2	10	6	2	-	-			6115-6x2	Enquiry
	6x3	12	6	3	-	-			6115-6x3	Enquiry
	7x1,5	10	7	1,5	-	-			6115-7x1,5	Enquiry
	7x2	11	7	2	-	-			6115-7x2	Enquiry
	7x3	13	7	3	-	-			6115-7x3	Enquiry
	8x1,5	11	8	1,5	-	-			6115-8x1,5	Enquiry
	8x2	12	8	2	-	-			6115-8x2	Enquiry
	8x3	14	8	3	-	-			6115-8x3	Enquiry
	9x2	13	9	2	-	-			6115-9x2	Enquiry
	10x2	14	10	2	-	-			6115-10x2	Enquiry
	12x2,5	17	12	2,5	-	-			6115-12x2,5	Enquiry
15x3	21	15	3	-	-			6115-15x3	Enquiry	

– Minimum order quantity 1m –

<b>Silicone fabric hose</b> 	DN	A	B	C	Pressure bar, 20 °C	Vacuum bar, 20 °C			Pressure hose VMQ	
	3x2,5	8	3	2,5	20	-			6116-3x2,5	Enquiry
	4x2,5	9	4	2,5	20	-			6116-4x2,5	Enquiry
	5x3	11	5	3	15	-			6116-5x3	Enquiry
	6x3	12	6	3	12	-			6116-6x3	Enquiry
	8x3	14	8	3	10	-			6116-8x3	Enquiry
	10x4	18	10	4	9	-			6116-10x4	Enquiry
	12x4	20	12	4	9	-			6116-12x4	Enquiry
	16x5	26	16	5	7	-			6116-16x5	Enquiry
	19x5,5	30	19	5,5	7	-			6116-19x5,5	Enquiry
	25x6	37	25	6	5	-			6116-25x6	Enquiry

– Minimum order quantity 1m – Silicone hoses with glass fabric core are not usable for pulsating pressures and duration of pressure applicatin on the limit of the max. operating pressure. Silicone hoses are not suitable for continuous stem, regular steam sterilization can lead to failure. In case of doubt please contact us.